

# AXEL

Yamato Scientific Co., Ltd.

61-9659-71-90 【Global Model】 Clean Oven DT611 DT611



DT411 DE611

Order No.	61-9659-71-90
Model No.	DT611
JAN Code	0000000000000
Std. Price	¥ 2,617,000(w/o tax)
Quantity	1piece

## Spec

- Circulation method: Forced air circulation
- Operating temp. range: RT+30~360°C
- Temp. adjustment accuracy:  $\pm 0.3^{\circ}\text{C}$  (at 360°C) JTM K05
- Temp. fluctuation: 1.0°C (at 360°C) JIS
- Temp. distribution accuracy:  $\pm 4.0^{\circ}\text{C}$  (at 360°C) JTM K05
- Temp. gradient: 20°C (at 360°C) JIS
- Max. temp. reaching time: Approx. 80 min (at 360°C)
- Clean level: Class 100 (when the temp. is stable)
- Internal dimensions(WxDxH): 600 x 600 x 600mm
- External dimensions(WxDxH): 850 x 1175 x 1720mm
- Internal capacity: Approx. 216L
- No. of steps: 17 steps
- Power supply: AC380V 50/60Hz Three phase 8A
- Weight: Approx. 270kg
- Accessories: Stainless shelf x 3, Shelf bracket x 6, Manual