

# AXEL

Yamato Scientific Co., Ltd.

**61-9659-80-90** 【Global Model】 Fine Oven (Tall) DFS710 DFS710



DHS710 DHS810

Order No.	61-9659-80-90
Model No.	DFS710
JAN Code	0000000000000
Std. Price	<b>¥ 737,000</b> (w/o tax)
Quantity	1piece

## Spec

- Circulation method: Forced air circulation and ventilation
- Operating temp. range: RT+15~260°C
- Max. temp. reaching time: Approx. 40 min (at 260°C)
- Temp. adjustment accuracy:  $\pm 0.2^{\circ}\text{C}$  (at 260°C) JTM K05
- Temp. distribution accuracy:  $\pm 2.0^{\circ}\text{C}$  (at 260°C) JTM K05
- Internal dimensions(WxDxH): 620 x 750 x 900mm
- External dimensions(WxDxH): 770 x 965 x 1580mm
- Internal capacity: Approx. 418L
- No. of steps/pitch: 27 steps/30mm
- Power supply: AC220V 50/60Hz single phase 21A (plug is not included)
- Weight: Approx. 175 kg
- Accessories: Stainless shelf x 2, Shelf bracket x 4, Manual