

# AXEL

Yamato Scientific Co., Ltd.

61-9659-81-90 【Global Model】 Fine Oven (Tall) DFS810 DFS810



DHS710 DHS810

Order No.	61-9659-81-90
Model No.	DFS810
JAN Code	0000000000000
Std. Price	¥ 1,253,000(w/o tax)
Quantity	1piece

## Spec

- Circulation method: Forced air circulation and ventilation
- Operating temp. range: RT+15~260°C
- Max. temp. reaching time: Approx. 40 min (at 260°C)
- Temp. adjustment accuracy:  $\pm 0.2^{\circ}\text{C}$  (at 260°C) JTM K05
- Temp. distribution accuracy:  $\pm 2.0^{\circ}\text{C}$  (at 260°C) JTM K05
- Internal dimensions(WxDxH): 620 x 750 x 1200mm
- External dimensions(WxDxH): 770 x 965 x 1880mm
- Internal capacity: Approx. 558L
- No. of steps/pitch: 37 steps/30mm
- Power supply: AC380V 50/60Hz Three phase 9A
- Weight: Approx. 190 kg
- Accessories: Stainless shelf x 2, Shelf bracket x 4, Manual