

AXEL

Yamato Scientific Co., Ltd.

61-9659-82-90 【Global Model】 Fine Oven (Tall) DHS710 DHS710



DHS710 DHS810

Order No.	61-9659-82-90
Model No.	DHS710
JAN Code	0000000000000
Std. Price	¥ 1,253,000(w/o tax)
Quantity	1piece

Spec

- Circulation method: Forced air circulation and ventilation
- Operating temp. range: RT+15~360°C
- Max. temp. reaching time: Approx. 50 min (at 360°C)
- Temp. adjustment accuracy: $\pm 0.3^{\circ}\text{C}$ (at 360°C) JTM K05
- Temp. distribution accuracy: $\pm 3.0^{\circ}\text{C}$ (at 360°C) JTM K05
- Internal dimensions(WxDxH): 620 x 750 x 900mm
- External dimensions(WxDxH): 770 x 965 x 1580mm
- Internal capacity: Approx. 418L
- No. of steps/pitch: 27 steps/30mm
- Power supply: AC380V 50/60Hz Three phase 9A
- Weight: Approx. 175 kg
- Accessories: Stainless shelf x 2, Shelf bracket x 4, Manual